

Hydrogen Break-away Coupling




TATSUNO




In Innovation, In Reliable Services

Break-away Coupling (for high-pressure hydrogen)

- **Safety break-away coupling prevents damage to dispensers and the release of gas into the environment in unexpected situations, such as operation mistakes after filling.**



Product Lineup

Flow Rate	NF / MF	HF
Model	H70	H70
Appearance		 
Dimensions (mm)	W147 × D60 × H191.5	W144 × D70.5 × H209
Mass	4.5kg	5.0kg
Maximum flow rate	90g/sec	300g/sec
Remarks	Silencer, filter with standard equipment	Equipped silencer



Hydrogen Business Department

1-1, Kasama 4-Chome, Sakae-Ku, Yokohama, 247-8570, Japan
 Telephone: +81-(0)50-9002-0723 Fax: +81-(0)45-891-1414

<https://tatsuno-corporation.com>

